



Pilot-operated, anti shock sequence cartridges limit maximum system pressure and also limit the rate of pressure rise. The valve opens and then ramps closed at a constant speed, independent of settings and flows. The adjust screw determines the maximum (relief) setting and the minimum (threshold) setting.

The external drain makes the valve insensitive to pressure at port 2.

TECHNICAL DATA

NOTE: DATA MAY VARY BY CONFIGURATION. SEE CONFIGURATION SECTION.

Factory Pressure Settings Established at	15 L/min.
Maximum Operating Pressure	350 bar
Control Pilot Flow	0,16 - 0,41 L/min.
Pressure Ramp Up Time	200 - 400 ms
Response Time - Typical	2 ms
Adjustment - No. of CW Turns from Min. to Max. setting	4.5
Locknut Hex Size	15 mm
Locknut Torque	9 - 10 Nm
Seal kit - Cartridge	Buna: 990402007
Seal kit - Cartridge	Polyurethane: 990002002
Seal kit - Cartridge	Viton: 990402006

CONFIGURATION OPTIONS

Model Code Example: SDFTLAN

CONTROL	(L)	ADJUSTMENT RANGE	(A)	SEAL MATERIAL	(N)
L Standard Screw Adjustment	A	2000 - 3000 psi (140 - 210 bar), 2000 psi (140 bar) Standard Setting	N	Buna-N	
	C	4500 - 6000 psi (315 - 420 bar), 4500 psi (315 bar) Standard Setting	V	Viton	
	W	3000 - 4500 psi (210 - 315 bar), 3000 psi (210 bar) Standard Setting			